

ステンレス角管(SUS304)

寸 法	HL	#400
26 × 51 × 1.2 × 5000	○	○
26 × 51 × 1.5 × 5000	○	○
26 × 51 × 2.0 × 5000	○	○
28.6 × 28.6 × 1.0 × 5000	○	○
28.6 × 28.6 × 1.2 × 5000	○	○
28.6 × 28.6 × 1.5 × 5000	○	○
30 × 30 × 1.2 × 5000	○	○
30 × 30 × 1.5 × 5000	○	○
30 × 50 × 1.5 × 5000	○	○
30 × 50 × 2.0 × 5000	○	
30 × 60 × 1.5 × 5000	○	○
30 × 60 × 2.0 × 5000	○	○
30 × 70 × 1.5 × 5000	○	○
30 × 70 × 2.0 × 5000	○	○
30 × 90 × 1.5 × 5000	○	○
30 × 90 × 2.0 × 5000	○	○
30 × 90 × 3.0 × 5000	○	
32 × 32 × 1.2 × 5000	○	○
32 × 32 × 1.5 × 5000	○	○
32 × 32 × 2.0 × 5000	○	
32 × 61 × 1.5 × 5000	○	○
32 × 61 × 2.0 × 5000	○	○
35 × 35 × 1.2 × 5000	○	○
35 × 35 × 1.5 × 5000	○	○
38.5 × 38.5 × 1.2 × 5000	○	○
38.5 × 38.5 × 1.5 × 5000	○	○
38.5 × 38.5 × 2.0 × 5000	○	○
40 × 40 × 1.5 × 5000	○	○
40 × 40 × 2.0 × 5000	○	○
40 × 60 × 1.5 × 5000	○	○
40 × 60 × 2.0 × 5000	○	○
40 × 80 × 1.5 × 5000	○	○
40 × 80 × 2.0 × 5000	○	○
40 × 80 × 3.0 × 5000	○	
40 × 100 × 2.0 × 5000	○	○

寸 法	HL	#400
40 × 100 × 3.0 × 5000	○	
41 × 41 × 1.2 × 5000	○	○
41 × 41 × 1.5 × 5000	○	○
41 × 41 × 2.0 × 5000	○	○
45 × 75 × 1.5 × 5000	○	○
45 × 75 × 2.0 × 5000	○	○
45 × 75 × 3.0 × 5000	○	
46 × 46 × 1.5 × 5000	○	○
46 × 46 × 2.0 × 5000	○	○
50 × 50 × 1.5 × 5000	○	○
50 × 50 × 2.0 × 5000	○	○
50 × 50 × 3.0 × 5000	○	○
50 × 90 × 1.5 × 5000	○	
50 × 90 × 2.0 × 5000	○	
50 × 90 × 3.0 × 5000	○	
50 × 100 × 2.0 × 5000	○	○
50 × 100 × 3.0 × 5000	○	○
50 × 150 × 2.0 × 5000	○	○
50 × 150 × 3.0 × 5000	○	
60 × 60 × 1.5 × 5000	○	○
60 × 60 × 2.0 × 5000	○	○
60 × 60 × 3.0 × 5000	○	○
60 × 120 × 2.0 × 5000	○	○
60 × 120 × 3.0 × 5000	○	
75 × 75 × 2.0 × 5000	○	○
75 × 75 × 3.0 × 5000	○	○
100 × 100 × 2.0 × 5000	○	○
100 × 100 × 3.0 × 5000	○	

ステンレス角管(SUS304)

寸 法	HL	#400
7 × 7 × 1.0 × 4000	○	○
9 × 9 × 0.8 × 4000	○	○
9 × 9 × 1.0 × 4000	○	○
10 × 10 × 1.0 × 4000	○	○
10 × 10 × 1.2 × 4000	○	○
10 × 19 × 1.0 × 4000	○	○
10 × 19 × 1.2 × 4000	○	○
12 × 12 × 1.0 × 4000	○	○
12 × 12 × 1.2 × 4000	○	○
12 × 22 × 1.0 × 5000	○	○
12 × 22 × 1.2 × 5000	○	○
12 × 22 × 1.5 × 5000	○	○
12 × 25 × 1.2 × 5000	○	○
12 × 25 × 1.5 × 5000	○	○
13 × 13 × 1.0 × 4000	○	○
13 × 13 × 1.2 × 4000	○	○
14 × 14 × 1.0 × 4000	○	○
14 × 14 × 1.2 × 4000	○	○
14 × 24 × 1.0 × 5000	○	○
14 × 24 × 1.2 × 5000	○	○
14 × 24 × 1.5 × 5000	○	○
14 × 24 × 2.0 × 5000	○	
16 × 16 × 1.0 × 5000	○	○
16 × 16 × 1.2 × 5000	○	○
16 × 16 × 1.5 × 5000	○	○
16 × 32 × 1.0 × 5000	○	
16 × 32 × 1.2 × 5000	○	○
16 × 32 × 1.5 × 5000	○	○
18 × 40 × 1.0 × 5000	○	○
18 × 40 × 1.2 × 5000	○	○
18 × 40 × 1.5 × 5000	○	○
18 × 65 × 1.2 × 5000	○	○
18 × 65 × 1.5 × 5000	○	○
19 × 19 × 1.0 × 5000	○	○
19 × 19 × 1.2 × 5000	○	○

寸 法	HL	#400
19 × 19 × 1.5 × 5000	○	○
19 × 19 × 2.0 × 5000	○	
20 × 20 × 1.2 × 5000	○	
20 × 20 × 1.5 × 5000	○	○
20 × 30 × 1.2 × 5000	○	○
20 × 30 × 1.5 × 5000	○	○
20 × 40 × 1.2 × 5000	○	○
20 × 40 × 1.5 × 5000	○	○
20 × 40 × 2.0 × 5000	○	
20 × 50 × 1.2 × 5000	○	
20 × 50 × 1.5 × 5000	○	○
21 × 21 × 1.0 × 5000	○	○
21 × 21 × 1.2 × 5000	○	○
21 × 21 × 1.5 × 5000	○	○
22 × 22 × 1.0 × 5000	○	
22 × 22 × 1.2 × 5000	○	
22 × 22 × 1.5 × 5000	○	○
24 × 24 × 1.0 × 5000	○	
24 × 24 × 1.2 × 5000	○	○
24 × 24 × 1.5 × 5000	○	○
25 × 25 × 1.2 × 5000	○	○
25 × 25 × 1.5 × 5000	○	○
25 × 30 × 1.2 × 5000	○	
25 × 30 × 1.5 × 5000	○	○
25 × 40 × 1.2 × 5000	○	○
25 × 40 × 1.5 × 5000	○	○
25 × 40 × 2.0 × 5000	○	
25 × 50 × 1.5 × 5000	○	○
25 × 50 × 2.0 × 5000	○	○
25 × 60 × 1.5 × 5000	○	○
25 × 60 × 2.0 × 5000	○	○
25 × 70 × 1.5 × 5000	○	○
25 × 70 × 2.0 × 5000	○	○
25.4 × 25.4 × 1.2 × 5000	○	○
25.4 × 25.4 × 1.5 × 5000	○	○